ASCO™ Manual Reset Valves


Normally Open or Normally Closed,
Brass or Stainless Steel Bodies, 1/2" to 2 1/2" NPT

2/2
Series
8015/8025

Features

- Designed to prevent inadvertent valve start-up
- Once tripped, requires electrical power restoration and manual operation to reset
- Electrically Tripped (trips when energized) or No Voltage Release (trips when de-energized) constructions
- Available for Latched Open or Latched Closed operation
- Ideal for controlling critical processes
- Handles air, inert gas, water, light oil, steam, and corrosive fluids





Construction

Valve Parts in Contact with Fluids		
Body	Brass	Stainless Steel
Stem	303 Stainless Steel	
Springs	302 Stainless Steel	
Disc, Diaphragm, Seat & Seal Material	FKM, NBR, PTFE, or EPDM, as listed	

Electrical

Standard Coil and Class of Insulation	Watt Rating and Power Consumption				Spare Coil Part Number	
	DC Watts	AC				
		Watts	VA Holding	VA Inrush	AC	DC
F	30.8	20.1	45	140	272610	501695
H	30.8	20.1	45	140	272810	440162

Standard Voltages: 24, 120, 240, 480 volts AC, 60 Hz. 6, 12, 24, 120, 240 volts DC. Must be specified when ordering. Other voltages are available when required.

Notes: 125 and 250 volts DC are battery voltages applied in power plants. Special valves are available to pilot control valves in power plants.

Consult your local ASCO sales office for a listing.

Solenoid Enclosures

Standard:

RedHat II - Watertight, types 1, 2, 3, 3S, 4, and 4X.

Optional:

RedHat II – Explosionproof and Watertight,
Types 3, 3S, 4, 4X, 6, 6P, 7, and 9.

See Optional Features Section for other available options.

Nominal Ambient Temp Ranges

General Purpose	
AC	Class F: -20˚F to 125˚F (-29˚C to 52˚C)
	Class H: -20˚F to 140˚F (-29˚C to 60˚C)
DC	Class F: -20˚F to 104˚F (-29˚C to 40˚C)
	Class H: -20˚F to 140˚F (-29˚C to 60˚C)
Explosion Proof (EF)	
AC/DC	Class F: -20˚F to 104˚F (-29˚C to 40˚C)
	Class H: -20˚F to 140˚F (-29˚C to 60˚C)

Approvals

UL & CSA Solenoid Approval only for explosion proof options ("EF" Prefix)

Refer to Engineering Section for details.

Operation Alternatives

Electrically Tripped – Valves move to latched position when the solenoid is de-energized, trips when they receive a continuous or momentary (at least 0.3 sec.) electrical signal. When tripped, they can be manually cycled open/closed, but must be reset when the solenoid has once again been de-energized.

No Voltage Release – Valves move to latched position when the solenoid is energized, trips when de-energized. When tripped, they can be manually cycled open/ closed, but must be reset when the solenoid has once again been energized.


Specifications (English units)


Pipe Size (in)	Orifice Size (in)	Cv Flow Factor	Operating Pressure Differential (psi)			Max. Fluid Temp. °F		Latched Open		Latched Closed		Watt Rating/ Class of Coil Insulation	
								No Voltage Release (closes when coil is de-energized)	Electrically Tripped (closes when coil is energized)	No Voltage Release (opens when coil is de-energized)	Electrically Tripped (opens when coil is energized)		
			Min.	Max. AC	Max. DC	AC	DC	Catalog Number	Catalog Number	Catalog Number	Catalog Number	AC	DC
BRASS BODY with NBR Diaphragm for Air, Inert Gas, Water, and Light Oil													
3/4	3/4	6.5	5	250	250	180	180	8025G201	8015G201	8025G214	8015G214	20.1/F	30.8/F
1	1	13	5	125	125	180	180	8025G202	8015G202	8025G215	8015G215	20.1/F	30.8/F
1 1/4	1 1/8	15	5	125	125	180	180	8025G203	8015G203	8025G216	8015G216	20.1/F	30.8/F
1 1/2	1 1/4	22.5	5	125	125	180	180	8025G204	8015G204	8025G217	8015G217	20.1/F	30.8/F
2	1 3/4	43	5	125	125	180	180	8025G205	8015G205	8025G218	8015G218	20.1/F	30.8/F
2 1/2	1 3/4	45	5	125	125	180	180	8025G206	8015G206	8025G219	8015G219	20.1/F	30.8/F
BRASS BODY with PTFE Disc (EPDM, FPM and PTFE Seals) for Steam Service													
3/4	3/4	7.8	5	125	125	353	353	8025G207	8015G207	8025G220	8015G220	20.1/F	30.8/F
1	1	13.5	5	125	125	353	353	8025G208	8015G208	8025G221	8015G221	20.1/F	30.8/F
1 1/4	1 1/8	15	5	125	125	353	353	8025G209	8015G209	8025G222	8015G222	20.1/F	30.8/F
1 1/2	1 1/4	22.5	5	125	125	353	353	8025G210	8015G210	8025G223	8015G223	20.1/F	30.8/F
STAINLESS STEEL BODY with PTFE Disc (FPM Seals) for Corrosive Service													
1/2	3/8	3.2	5	250	250	350	350	8025G211	8015G211	8025G224	8015G224	20.1/F	30.8/F
3/4	3/4	7.8	5	250	250	350	350	8025G212	8015G212	8025G225	8015G225	20.1/F	30.8/F
1	1	11.2	5	125	125	350	350	8025G213	8015G213	8025G226	8015G226	20.1/F	30.8/F


Specifications (Metric units)

Pipe Size (in)	Orifice Size (mm)	Kv Flow Factor (m^3/h)	Operating Pressure Differential (bar)			Max. Fluid Temp. °C		Latched Open		Latched Closed		Watt Rating/ Class of Coil Insulation	
								No Voltage Release (closes when coil is de-energized)	Electrically Tripped (closes when coil is energized)	No Voltage Release (opens when coil is de-energized)	Electrically Tripped (opens when coil is energized)		
			Min.	Max. AC	Max. DC	AC	DC	Catalog Number	Catalog Number	Catalog Number	Catalog Number	AC	DC
BRASS BODY with NBR Diaphragm for Air, Inert Gas, Water, and Light Oil													
3/4	19	5.57	0.3	17	17	82	82	8025G201	8015G201	8025G214	8015G214	20.1/F	30.8/F
1	25	11.14	0.3	9	9	82	82	8025G202	8015G202	8025G215	8015G215	20.1/F	30.8/F
1 1/4	29	12.86	0.3	9	9	82	82	8025G203	8015G203	8025G216	8015G216	20.1/F	30.8/F
1 1/2	32	19.29	0.3	9	9	82	82	8025G204	8015G204	8025G217	8015G217	20.1/F	30.8/F
2	44	36.86	0.3	9	9	82	82	8025G205	8015G205	8025G218	8015G218	20.1/F	30.8/F
2 1/2	44	38.57	0.3	9	9	82	82	8025G206	8015G206	8025G219	8015G219	20.1/F	30.8/F
BRASS BODY with PTFE Disc (EPDM, FPM and PTFE Seals) for Steam Service													
3/4	19	6.69	0.3	9	9	177	177	8025G207	8015G207	8025G220	8015G220	20.1/F	30.8/F
1	25	11.57	0.3	9	9	177	177	8025G208	8015G208	8025G221	8015G221	20.1/F	30.8/F
1 1/4	29	12.86	0.3	9	9	177	177	8025G209	8015G209	8025G222	8015G222	20.1/F	30.8/F
1 1/2	32	19.29	0.3	9	9	177	177	8025G210	8015G210	8025G223	8015G223	20.1/F	30.8/F
STAINLESS STEEL BODY with PTFE Disc (FPM Seals) for Corrosive Service													
1/2	10	2.74	0.3	17	17	175	175	8025G211	8015G211	8025G224	8015G224	20.1/F	30.8/F
3/4	19	6.69	0.3	17	17	175	175	8025G212	8015G212	8025G225	8015G225	20.1/F	30.8/F
1	25	9.60	0.3	9	9	175	175	8025G213	8015G213	8025G226	8015G226	20.1/F	30.8/F

Dimensions: inches (mm)









Catalog Number		A		B		C		T		R		P	
		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC
8025G201 8025G214	in	5.2	5.4	5.8	6.3	2.2	2.4	4.9	4.8	3.4	3.4	2.2	2.1
	mm	131	136	148	153	57	63	124	122	88	87	56	54
8015G201 8015G214	in	5.2	5.4	5.8	6.3	2.2	2.4	4.8	4.8	3.4	3.4	2.2	2.3
	mm	131	136	148	153	57	63	123	122	88	87	56	58


Dimensions: inches (mm)




Catalog Number		A		B		C		D		E		F		G		H		K		T		R		P		V	
		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC
8025G202	in	2.1	2.1	3.8	3.8	7.3	7.5	4.9	4.9	6	6	4.6	4.6	8.1	8.1	5.7	5.9	5.2	5.2	4.9	4.8	3.5	3.4	2.2	2.1	0.4	0.5
8025G215	mm	52	52	95	95	185	190	125	124	152	152	118	118	205	205	144	149	133	133	124	123	88	87	56	54	12	12
8015G202	in	2.1	2.1	3.8	3.8	7.3	7.5	4.9	4.9	6	6	4.6	4.6	8.1	8.1	5.7	5.9	5.2	5.2	4.9	4.8	3.5	3.4	2.2	2.3	0.4	0.5
8015G215	mm	52	52	95	95	185	190	125	124	152	152	118	118	205	205	144	149	133	133	124	123	88	87	56	58	12	12
8025G203	in	2.1	2.1	3.7	3.7	7.3	7.5	5.1	5	5.9	5.9	4.6	4.6	8.1	8.1	5.7	5.9	5.2	5.2	4.8	4.8	3.5	3.5	2.2	2.1	0.5	0.5
8025G216	mm	52	52	93	93	185	190	131	130	148	149	118	118	205	205	144	149	133	133	122	123	88	88	56	54	13	13
8015G203	in	2.1	2.1	3.7	3.7	7.3	7.5	5.1	5	5.9	5.9	4.6	4.6	8.1	8.1	5.7	5.9	5.2	5.2	4.9	4.8	3.5	3.5	2.2	2.1	0.5	0.5
8015G216	mm	52	52	93	93	185	190	131	130	148	149	118	118	205	205	144	149	133	133	124	123	88	88	56	54	13	13
8025G204	in	2.2	2.2	4.4	4.4	7.8	8	5.4	5.4	6.4	6.4	4.8	4.8	8.2	8.2	5.8	6	5.4	5.4	4.8	4.8	3.5	3.4	2.2	2.1	0.7	0.7
8025G217	mm	56	56	111	111	197	202	139	139	164	164	121	121	208	208	148	152	137	137	123	123	88	87	56	54	18	18
8015G204	in	2.2	2.2	4.4	4.4	7.8	8	5.4	5.4	6.4	6.4	4.8	4.8	8.2	8.2	5.8	6	5.4	5.4	4.8	4.8	3.5	3.4	2.2	2.1	0.7	0.7
8015G217	mm	56	56	111	111	197	202	139	139	164	164	121	121	208	208	148	152	137	137	123	123	88	87	56	54	18	18
8025G221	in	3.8	3.8	2.1	2.1	5.7	5.9	5.2	5.2	8.1	8.1	7.3	7.5	5.8	5.8	3.1	3.1	2.2	2.5	4.9	4.8	3.5	3.4	2.2	2.1	5.5	5.5
8025G208	mm	95	95	52	52	144	149	131	131	206	206	185	190	147	147	80	80	57	63	124	122	88	87	57	54	140	139
8015G221	in	3.8	3.8	2.1	2.1	5.7	5.9	5.2	5.2	8.1	8.1	7.3	7.5	5.8	5.8	3.1	3.1	2.2	2.5	4.8	4.8	3.4	3.4	2.2	2.3	5.5	5.5
8015G208	mm	95	95	52	52	144	149	131	131	206	206	185	190	147	147	80	80	57	63	122	122	86	87	57	58	138	139
8025G222	in	3.7	3.7	2	2	5.7	5.9	5.2	5.2	8.1	8.1	7.3	7.5	6	6	3.6	3.6	2.2	2.5	4.9	4.8	3.5	3.4	2.2	2.1	5.5	5.5
8025G209	mm	93	93	52	52	144	149	131	131	206	206	185	190	152	152	91	91	57	63	124	122	88	87	57	54	140	139
8015G222	in	3.7	3.7	2	2	5.7	5.9	5.2	5.2	8.1	8.1	7.3	7.5	6	6	3.6	3.6	2.2	2.5	4.8	4.8	3.4	3.4	2.2	2.3	5.5	5.5
8015G209	mm	93	93	52	52	144	149	131	131	206	206	185	190	152	152	91	91	57	63	122	122	86	87	57	58	138	139
8025G223	in	4.4	4.4	2.2	2.2	5.7	5.9	5.6	5.6	8.6	8.6	7.8	8	6.3	6.3	4.1	4.1	2.2	2.5	4.9	4.8	3.5	3.4	2.2	2.1	5.7	5.6
8025G210	mm	111	111	56	56	144	149	143	143	218	218	197	202	161	161	104	104	57	63	124	122	88	87	57	54	144	143
8015G223	in	4.4	4.4	2.2	2.2	5.7	5.9	5.6	5.6	8.6	8.6	7.8	8	6.3	6.3	4.1	4.1	2.2	2.5	4.8	4.8	3.4	3.4	2.2	2.3	5.6	5.6
8015G210	mm	111	111	56	56	144	149	143	143	218	218	197	202	161	161	104	104	57	63	122	122	86	87	57	58	142	143

Dimensions: inches (mm)









Catalog Number		A		B		C		T		R		P	
		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC
8025G207 8025G220	in	5.1	5.3	6.5	6.7	2.2	2.5	4.9	4.8	3.4	3.4	2.1	2.1
	mm	129	134	165	170	57	63	124	122	88	86	56	54
8015G207 8015G220	in	5.1	5.3	6.5	6.7	2.2	2.5	4.8	4.8	3.4	3.4	2.1	2.1
	mm	129	134	165	170	57	63	122	122	86	87	56	54
8025G211 8025G224	in	4.6	4.8	5.7	5.9	2.2	2.4	4.9	4.8	3.4	3.4	2.2	2.1
	mm	117	122	146	151	57	63	124	123	88	87	57	54
8015G211 8015G224	in	4.6	4.8	5.7	5.9	2.2	2.4	4.8	4.8	3.4	3.4	2.2	2.3
	mm	117	122	146	151	57	63	123	123	88	86	57	58

Dimensions: inches (mm)




Catalog Number		A		B		C		D		E		F		G		T		R		P		V	
		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC
8025G205 8025G218	in	5.9	5.9	7.5	7.5	2.2	2.5	5.5	5.5	5.6	5.6	6.2	6.4	9	9.2	4.9	4.9	3.5	3.5	2.2	2.1	0.5	0.5
	mm	95	95	190	190	57	63	140	140	142	142	158	163	229	233	123	123	88	88	57	54	13	13
8015G205 8015G218	in	5.9	5.9	7.5	7.5	2.2	2.5	5.5	5.5	5.6	5.6	6.2	6.4	9	9.2	4.8	4.9	3.4	3.5	2.2	2.3	0.5	0.5
	mm	95	95	190	190	57	63	139	140	142	142	158	163	229	233	122	123	87	88	57	58	13	13
8025G206 8025G219	in	4.1	4.1	5.5	5.5	2.2	2.5	6	6	5.6	5.6	6.2	6.4	9	9.2	4.9	4.9	3.5	3.5	2.2	2.1	0.7	0.7
	mm	105	105	140	140	57	63	153	153	144	144	158	163	229	233	124	123	88	88	57	54	19	19
8015G206 8015G219	in	4.1	4.1	5.5	5.5	2.2	2.5	6	6	5.6	5.6	6.2	6.4	9	9.2	4.9	4.9	3.4	3.5	2.2	2.3	0.7	0.7
	mm	105	105	140	140	57	63	152	153	144	144	158	163	229	233	124	123	87	88	57	58	19	19

Dimensions: inches (mm)




Catalog Number		A		B		C		T		R		P		W	
		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC
8025G213 8025G226	in	5.7	5.9	7.3	7.5	2.2	2.5	4.9	4.9	3.5	3.5	2.1	2.1	5.5	5.5
	mm	144	149	185	190	57	63	123	123	88	88	56	54	140	140
8015G213 8015G226	in	5.7	5.9	7.3	7.5	2.2	2.5	4.8	4.9	3.4	3.5	2.1	2.3	5.4	5.5
	mm	144	149	185	190	57	63	122	123	87	88	56	58	139	140


Dimensions: inches (mm)




Catalog Number		A		B		C		D		E		F		G		H		J		K		L		M		P	
		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC
8025G225	in	5.2	5.5	1.6	1.7	2.2	2.5	5.2	5.2	4	3.9	6.6	6.8	3.9	4.1	5.9	5.9	6.6	6.8	2.1	2.5	4.8	4.8	3.4	3.4	2.1	2.1
	mm	132	139	42	42	56	63	132	132	101	99	167	172	99	105	149	150	167	172	52	62	123	123	88	87	56	54
8025G212	in	5.3	5.5	1.7	1.7	2.2	2.5	5.2	5.2	3.9	3.9	6.6	6.8	3.9	4.1	6.3	6.7	6.6	6.8	2.1	2.5	4.8	4.8	3.4	3.4	2.1	2.1
	mm	133	139	42	42	57	63	131	131	99	99	167	172	99	105	161	169	167	172	52	62	122	123	87	87	56	54
8015G225	in	5.3	5.5	1.7	1.7	2.2	2.5	5.2	5.2	3.9	4	6.6	6.8	4	3.9	6.3	5.9	6.6	6.8	2.1	2.5	4.9	4.8	3.4	3.4	2.1	2.2
	mm	134	139	44	42	56	63	132	131	100	103	167	172	101	100	161	151	167	172	52	62	125	123	87	87	56	58
8015G212	in	5.3	5.5	1.7	1.7	2.2	2.5	5.2	5.2	3.9	4	6.6	6.8	4	4.2	6.3	6.3	6.6	6.8	2.1	2.5	4.9	4.9	3.4	3.4	2.1	2.2
	mm	134	140	44	43	56	62	132	131	99	102	167	172	101	106	161	161	167	172	52	62	124	124	87	86	56	57

Dimensions: inches (mm)








Catalog Number		A		B		C		T		R		P	
		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC
8025G207 8025G220	in	5.1	5.3	6.5	6.7	2.2	2.5	4.9	4.8	3.4	3.4	2.1	2.1
	mm	129	134	165	170	57	63	124	122	88	86	56	54
8015G207 8015G220	in	5.1	5.3	6.5	6.7	2.2	2.5	4.8	4.8	3.4	3.4	2.1	2.1
	mm	129	134	165	170	57	63	122	122	86	87	56	54
8025G211 8025G224	in	4.6	4.8	5.7	5.9	2.2	2.4	4.9	4.8	3.4	3.4	2.2	2.1
	mm	117	122	146	151	57	63	124	123	88	87	57	54
8015G211 8015G224	in	4.6	4.8	5.7	5.9	2.2	2.4	4.8	4.8	3.4	3.4	2.2	2.3
	mm	117	122	146	151	57	63	123	123	88	86	57	58

Dimensions: inches (mm)



Catalog Number		A		B		C		D		E		F		G		H		K		T		R		P		V	
		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC
8025G202	in	2.1	2.1	3.8	3.8	7.3	7.5	4.9	4.9	6	6	4.6	4.6	8.1	8.1	5.7	5.9	5.2	5.2	4.9	4.8	3.5	3.4	2.2	2.1	0.4	0.5
8025G215	mm	52	52	95	95	185	190	125	124	152	152	118	118	205	205	144	149	133	133	124	123	88	87	56	54	12	12
8015G202	in	2.1	2.1	3.8	3.8	7.3	7.5	4.9	4.9	6	6	4.6	4.6	8.1	8.1	5.7	5.9	5.2	5.2	4.9	4.8	3.5	3.4	2.2	2.3	0.4	0.5
8015G215	mm	52	52	95	95	185	190	125	124	152	152	118	118	205	205	144	149	133	133	124	123	88	87	56	58	12	12
8025G203	in	2.1	2.1	3.7	3.7	7.3	7.5	5.1	5	5.9	5.9	4.6	4.6	8.1	8.1	5.7	5.9	5.2	5.2	4.8	4.8	3.5	3.5	2.2	2.1	0.5	0.5
8025G216	mm	52	52	93	93	185	190	131	130	148	149	118	118	205	205	144	149	133	133	122	123	88	88	56	54	13	13
8015G203	in	2.1	2.1	3.7	3.7	7.3	7.5	5.1	5	5.9	5.9	4.6	4.6	8.1	8.1	5.7	5.9	5.2	5.2	4.9	4.8	3.5	3.5	2.2	2.1	0.5	0.5
8015G216	mm	52	52	93	93	185	190	131	130	148	149	118	118	205	205	144	149	133	133	124	123	88	88	56	54	13	13
8025G204	in	2.2	2.2	4.4	4.4	7.8	8	5.4	5.4	6.4	6.4	4.8	4.8	8.2	8.2	5.8	6	5.4	5.4	4.8	4.8	3.5	3.4	2.2	2.1	0.7	0.7
8025G217	mm	56	56	111	111	197	202	139	139	164	164	121	121	208	208	148	152	137	137	123	123	88	87	56	54	18	18
8015G204	in	2.2	2.2	4.4	4.4	7.8	8	5.4	5.4	6.4	6.4	4.8	4.8	8.2	8.2	5.8	6	5.4	5.4	4.8	4.8	3.5	3.4	2.2	2.1	0.7	0.7
8015G217	mm	56	56	111	111	197	202	139	139	164	164	121	121	208	208	148	152	137	137	123	123	88	87	56	54	18	18
8025G221	in	3.8	3.8	2.1	2.1	5.7	5.9	5.2	5.2	8.1	8.1	7.3	7.5	5.8	5.8	3.1	3.1	2.2	2.5	4.9	4.8	3.5	3.4	2.2	2.1	5.5	5.5
8025G208	mm	95	95	52	52	144	149	131	131	206	206	185	190	147	147	80	80	57	63	124	122	88	87	57	54	140	139
8015G221	in	3.8	3.8	2.1	2.1	5.7	5.9	5.2	5.2	8.1	8.1	7.3	7.5	5.8	5.8	3.1	3.1	2.2	2.5	4.8	4.8	3.4	3.4	2.2	2.3	5.5	5.5
8015G208	mm	95	95	52	52	144	149	131	131	206	206	185	190	147	147	80	80	57	63	122	122	86	87	57	58	138	139
8025G222	in	3.7	3.7	2	2	5.7	5.9	5.2	5.2	8.1	8.1	7.3	7.5	6	6	3.6	3.6	2.2	2.5	4.9	4.8	3.5	3.4	2.2	2.1	5.5	5.5
8025G209	mm	93	93	52	52	144	149	131	131	206	206	185	190	152	152	91	91	57	63	124	122	88	87	57	54	140	139
8015G222	in	3.7	3.7	2	2	5.7	5.9	5.2	5.2	8.1	8.1	7.3	7.5	6	6	3.6	3.6	2.2	2.5	4.8	4.8	3.4	3.4	2.2	2.3	5.5	5.5
8015G209	mm	93	93	52	52	144	149	131	131	206	206	185	190	152	152	91	91	57	63	122	122	86	87	57	58	138	139
8025G223	in	4.4	4.4	2.2	2.2	5.7	5.9	5.6	5.6	8.6	8.6	7.8	8	6.3	6.3	4.1	4.1	2.2	2.5	4.9	4.8	3.5	3.4	2.2	2.1	5.7	5.6
8025G210	mm	111	111	56	56	144	149	143	143	218	218	197	202	161	161	104	104	57	63	124	122	88	87	57	54	144	143
8015G223	in	4.4	4.4	2.2	2.2	5.7	5.9	5.6	5.6	8.6	8.6	7.8	8	6.3	6.3	4.1	4.1	2.2	2.5	4.8	4.8	3.4	3.4	2.2	2.3	5.6	5.6
8015G210	mm	111	111	56	56	144	149	143	143	218	218	197	202	161	161	104	104	57	63	122	122	86	87	57	58	142	143

Availability, design and specifications are subject to change without notice.
© 2025 Emerson Electric Co. All rights reserved.